




EXT-440CU is a compact ambient liquid cooling system designed with features for computer cooling. This model contains a single x 120mm fan copper/brass radiator, providing roughly 400W of cooling with a 25° C ambient delta. Just add tubing, fittings, [coolant](#), and connect to your cold plate(s).

- Cooling capacity: 400W (1365BTU/hr) with 25° C liquid-ambient delta @ 4.5LPM
- Radiator fan speed: automatic based on temperature, or 10 manual levels
- Pump: 10 manual levels, up to 4.5LPM (1.2GPM)
- Adjust audio alarm based on 3 included temperature sensors
- Relay trigger can be adjusted based on temperature
- Power input: 12VDC (via computer Molex plug), or 110/220VAC with separate [adapter](#)
- Reservoir capacity: 157ml (5.3 fl oz)
- G 1/4 BSPP threads on back for fittings

General	
Weight	5.50 lb (2.49 kg)
Max Pressure @ 25° C	2kgf/cm2 (28.5psi)
Max Temperature	60° C (140° F)
Noise (dBA)	32-44
Cooling Systems	
Cooling Capacity	400W (1365BTU/hr) @ 25° C liquid-ambient (25° C dT)
Display Type	LED
Flow Rate	4.5LPM (1.2GPM)
Max Power Consumption	17W
Power Source	12 VDC (110/220 VAC with Separate Adapter)
Radiator	Brass/Copper, 1 x 120mm fan
Temperature Sensors	10K Thermistors

EXT-440
($\Delta T = \text{Inlet Water} - \text{Ambient} = 25^\circ\text{C}$)



EXT-440
($\Delta T = \text{Inlet Water} - \text{Ambient}$)

