


GPU-200 Cold Plate, 45mm x 45mm (1.8in x 1.8in)



The GPU-200 is a general-purpose block with a square peg array internal structure. The cooling area footprint is 45mm x 45mm (1.8in x 1.8in). Materials include a copper cold plate, brass top, anti-corrosive nickel plating, and EPDM o-ring. G 1/4 BSPP (parallel) thread.

The included bracket adjusts for diagonal mounting hole distances from approximately 65mm to 124mm (2.56in to 4.9in).

Cold Plates	
Flow Resistance @ 5LPM (10-13mm ID)	0.049kgf/cm ² (0.7psi)
Thermal Resistance @ 5LPM (Approx.)	0.07°C/W
General	
Weight	0.50 lb (0.23 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	10kgf/cm ² (142.2psi)
Max Temperature Tolerance	100°C (212°F)
Wetted Materials	Nickel-Plated Copper, Nickel-Plated Brass, EPDM



GPU-200

