


Radiator, 2x120mm Fans, 54mm Thick, 30-FPI  
Copper




HX-240XC is an extra thick (54mm, 2.1in) copper core radiator with a fin density of 30 FPI (fins per inch). It offers greatest performance when sandwiched between multiple high speed 120mm fans. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans on one side only (see Koolance [radiator screw packs](#) for additional options).

General	
Weight	2.60 lb (1.18 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	1.5kgf/cm2 (21psi)
Max Temperature Tolerance	150°C (302°F)
Wetted Materials	Brass/Copper
Radiators	
Fan Capacity	2 x 120mm
Fins Per Inch (FPI)	30


10-13mm ID Tubing




Koolance HX-240XC  
 $(\Delta T = \text{Inlet Water} - \text{Ambient} = 15^\circ\text{C})$



Koolance HX-240XC  
 $(\Delta T = \text{Inlet Water} - \text{Ambient} = 25^\circ\text{C})$



Koolance HX-240XC  
 $(\Delta T = \text{Inlet Water} - \text{Ambient})$



6mm ID Tubing

