





Create a swiveling 90 degree elbow bend using any Koolance G 1/4 BSPP (parallel) thread fitting. For a basic elbow fitting, the [Koolance Coupling Adapter](#) could also be used. Or for maximum adjustment, consider placing two swiveling elbow fittings together.

| General | |
|-------------------------------|---------------------|
| Weight | 0.08 lb (0.04 kg) |
| Fitting Thread | G 1/4 BSPP |
| Max Pressure Tolerance @ 25°C | 8kgf/cm2 (113.8psi) |
| Max Temperature Tolerance | 100°C (212°F) |
| Wetted Materials | Brass, EPDM |



| | | | | | | | | |
|---|-------------|---------|----|----|-----------|-----|---------------------|---------|
| | | | | | | | | |
| NO. | DESCRIPTION | | | | MATER'L | | QUANTITY | REMARKS |
|  | | | | | UNIT | MM | APPAR NZL-LXG1(-BK) | |
| <div>APPRO BY</div> | | | | | SCALE | N/S | TITLE | |
| | | | | | 3RD ANGLE | | Ass'y | |
| DATE | | BY | BY | BY | REF. NO. | | DWG. NO. | |
| | | S.J.LEE | | | | | | |
| | | | | | | | | |

| | | | | | | |
|----------|------|----------|---------|---------|---------|--|
| | | | | | | |
| | | | | | | |
| | | | | | | |
| | | | | | | |
| REV | DATE | CONTENTS | REVD BY | CHKD BY | APPD BY | |
| REVISION | | | | | | |