



The copper core HX-CU-1402V is designed for two 140mm fans. With a high fin density of 30 FPI (fins per inch), it offers best performance at higher air flow. Vertical (perpendicular) G 1/4 BSPP (parallel) thread fitting sockets, dual pass, 30mm (1.18") long mounting screws included.

General	
Weight	2.10 lb (0.95 kg)
Max Pressure Tolerance @ 25° C	1.5kgf/cm2 (21psi)
Max Temperature Tolerance	150° C (302° F)
Wetted Materials	Brass/Copper
Radiators	
Fan Capacity	2 x 140mm
Fins Per Inch (FPI)	30