

**HD-60 Cold Plate for 3.5in Hard Drives, 100mm x 146mm (3.9in x 5.7in)**








The double sided Koolance HD-60 captures heat from the spindle motor and printed circuit boards of one or two 3.5-inch IDE, SATA, SCSI, or SAS drives. The HD-60 allows any available fitting diameter.

The HD-60 is an all-metal water block, providing a thin profile of just 5/16in (8.5mm) for single or dual hard drive cooling. One bi-pack of thermal encapsulate is provided with the HD-60 for cooling a single hard drive. A [Second Hard Drive Kit](#) is required if cooling two drives.

NOTE: The HD-60 water block may not work in all systems. If your chassis places the hard drive connections near a side panel (perpendicular to the front), make sure there is sufficient clearance for the HD-60. For a better understanding of compatibility, [please click here](#).

| General                       |  |
|-------------------------------|--|
| Weight                        | 1.12 lb (0.51 kg)  |
| Max Pressure Tolerance @ 25°C | 2kgf/cm2 (28.5psi)   |
| Max Temperature Tolerance     | 100°C (212°F)  |
| Wetted Materials              | Nickel-Plated Copper, Nickel-Plated Brass, Stainless Steel, EPDM |





| NO.        | DESCRIPTION     | MATER'L |     | QUANTITY | REMARKS  |
|------------|-----------------|---------|-----|----------|----------|
|            | <b>KOOLANCE</b> | UNIT    | MM  | APPAR    | HD-60    |
|            |                 | SCALE   | N/S | TITLE    |          |
| DATE       | BY              | BY      | BY  | APPRO BY | Ass'y    |
| 04/11/2017 | S.J.LEE         |         |     |          | DWG. NO. |
|            |                 |         |     |          |          |