


Radiator, 3x120mm Fans, 54mm Thick, 30-FPI  
Copper




HX-360XC is an extra thick (54mm, 2.1in) copper core radiator with a fin density of 30 FPI (fins per inch). It offers greatest performance when sandwiched between multiple high speed 120mm fans. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans on one side only (see Koolance [radiator screw packs](#) for additional options).

General	
Weight	3.50 lb (1.59 kg)
Fitting Thread	G 1/4 BSPP
Materials	Brass/Copper
Max Pressure @ 25 °C	2kgf/cm2 (28.5psi)
Max Temperature	150 °C (302 °F)
Radiators	
Fan Capacity	3 x 120mm
Fins Per Inch (FPI)	30


6mm ID Tubing




Koolance HX-360XC  
 $(\Delta T = \text{Inlet Water} - \text{Ambient})$




Koolance HX-360XC  
 $(\Delta T = \text{Inlet Water} - \text{Ambient} = 25^\circ\text{C})$




Koolance HX-360XC  
 $(\Delta T = \text{Inlet Water} - \text{Ambient} = 15^\circ\text{C})$



### 10-13mm ID Tubing





REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
REVISION					

NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
<b>KOOLANCE</b>		UNIT	MM	ITEM HX-360XC
		SCALE	N/S	TITLE
DATE	BY	BY	BY	BY
	S.J.LEE			
		3RD ANGLE		
		CODE NO.		
			DWG. NO.	PAGE

Ass'y