





INS-FM18D Coolant Flow Meter with Display



INS-FM18D combines an LCD display with Koolance's stainless steel flow meter in a small footprint. The display shows flow rate in liters per minute (LPM) only. A 12VDC connection is required for power. Primary materials are a stainless steel body with nickel-plated brass G 1/4 BSPP threads.

Flow Meters	
Accuracy (Approx.)	+/-5%
Flow Rate Range	2.0-15 LPM (32-240 GPH)
General	
Weight	0.28 lb (0.13 kg)
Fitting Thread	G 1/4 BSPP
Materials	Nickel-Plated Brass, Brass, PMMA Acrylic, Stainless Steel, POM Acetal, Plastic, SmCo5
Max Pressure @ 25 °C	10kgf/cm2 (142.2psi)
Max Temperature	100 °C (212 °F)
Min Temperature	0 °C (32 °F)



NO.	DESCRIPTION	MATER'L		QUANTITY	REMARKS
	Koolance	UNIT	MM	PART NO.	INS-FM18D
		SCALE	N/S	TITLE	Ass'y
DATE	BY	BY	APPRO BY	3RD ANGLE	
05/15/2017	S.J.LEE			DWG. NO.	ITEM