



HX-CU1320VS is a low profile copper core radiator designed for four 120mm fans. With a fin density of 20 FPI (fins per inch), it is optimized for quieter air flow ranges. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).

General	
Weight	2.80 lb (1.27 kg)
Max Pressure Tolerance @ 25 °C	3kgf/cm2 (42.7psi)
Max Temperature Tolerance	150 °C (302 °F)
Wetted Materials	Brass/Copper
Radiators	
Fan Capacity	4 x 120mm
Fins Per Inch (FPI)	20

