

Koolance 702 Liquid Coolant, High-Performance, Colorless, 700ml (24 fl oz)



Koolance 702 series coolant is used by many industries requiring a high performance, low-toxicity, reliable coolant with corrosion and biological inhibitors. A high quality coolant is extremely important for addressing dissimilar metals and biologic growth (bacterial and algae) long-term. Koolance liquids will not clog components and can typically be used for 2-3 years before replacement is recommended. (Coolant shelf life is 3 years.)

This container includes 700ml (24 fl oz) of prediluted coolant and can function as a squirt bottle for convenient reservoir filling. It's recommended to replace the coolant at least every 2-3 years, or immediately if there is any change in color or clarity.

The freezing point is -15°C (5°F). This coolant has been

tested with the following materials:

- Metals: copper, brass, aluminum, stainless steel, nickel, steel, gold, lead
- Plastics: ABS, PA66, PBT, PE, PEI, PES, PETG, PMMA, POM, PP, PPE, PPO, PPS, PTFE, PU, PVC
- Rubber: EPDM

NOTE: Not recommended for polycarbonate plastics or other PC-based plastics.

| General | |
|---------------------------------|---------------------|
| Weight | 2.10 lb (0.95 kg) |
| Liquid Coolant | |
| Color | Clear |
| Electrical Conductivity (µS/cm) | 2500 |
| Freezing Point | -15°C (5°F) |
| Specific Gravity @20°C | 1.03 |
| UV Reactive | No |
| Viscosity @20°C (cP) | 2.3 |
| Volume | 700mL (23.67 fl oz) |