www.koolance.com

Specifications Sheet

Generated: 2026-11-10

P/N: HX-CU1320VS

Radiator, 4x120mm 20-FPI Copper



HX-CU1320VS is a low profile copper core radiator designed for four 120mm fans. With a fin density of 20 FPI (fins per inch), it is optimized for quieter air flow ranges. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance radiator screw packs for additional options).

General	
Weight	2.80 lb (1.27 kg)
Max Pressure Tolerance @ 25°C	3kgf/cm2 (42.7psi)
Max Temperature Tolerance	150°C (302°F)
Wetted Materials	Brass/Copper
Radiators	
Fan Capacity	4 x 120mm
Fins Per Inch (FPI)	20



