



Koolance infrared liquid level sensor. Total length of sensor = 29mm (1.14in). Nickel plated brass, G 1/4 BSPP threading.

- Input: 5-12VDC
- Output: 0V when in liquid, 3.5-10.5V in air
- Current: 20mA max @ 12V
- Connector: Molex 5264, 3-wire
- Pinout: blue = output, black = ground, red = input (5-12VDC)
- Wire length: 700mm

General	
Weight	0.08 lb (0.04 kg)
Fitting Thread	G 1/4 BSPP
Materials	Nickel-Plated Brass, EPDM, PMMA Acrylic
Max Pressure @ 25° C	1.5kgf/cm <sup>2</sup> (21.3psi)
Max Temperature	70° C (158° F)

