




INS-FM19 Coolant Flow Meter, Reed Switch



Koolance's inline flow meters provide electronic indication of real-time coolant flow rate. This model uses a reed switch to detect impeller rotation. G 1/4 BSPP fitting threads, and primary materials are nickel-plated brass and acrylic. Approximate read range is 1.0-20 LPM (15.6-317 GPH). Wire length is about 28" (70cm). INS-FM19 is identical to INS-FM17N, but has an external metal shell for greater durability. It is recommended to keep current through the flow meter at 10mA or less to prevent damage.

Flow Meters	
Accuracy (Approx.)	+/-5%
Flow Rate Range	1.0-20 LPM (15.6-317 GPH)
General	
Weight	0.16 lb (0.07 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	5kgf/cm2 (71.1psi)
Max Temperature Tolerance	70° C (158° F)
Min Storage Temperature (*No Freezing)	0° C (32° F)
Wetted Materials	Nickel-Plated Brass, PTFE, PMMA Acrylic, Stainless Steel, POM Acetal, PBT, SmCo5





REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
REVISION					

NO.		DESCRIPTION				MATER'L		QUANTITY	REMARKS
KOLANCE						UNIT	MM	ITEM INS-FM19	
						SCALE	N/S	TITLE	
		BY	BY	BY	APPRO BY	Ass'y			
DATE						3RD ANGLE			
JAN.20.2025		S.J.LEE				CODE NO.		DWG. NO.	
								PAGE	