

ALX-750-P400 Modular Liquid Cooling System (Rev.2.0)



Koolance's ALX series are powerful liquid cooling systems with expandable thermal capacities and software logging. ALX-750-P400 provides approximately 750W of cooling using a single fan radiator.

This version includes the RPM-ALX400 and HXM-ALX750 modules. These are quickly combined during installation, and [individually upgradeable](#) if requirements later change. The front "RPM" contains the pump, reservoir, electronics, and sensors. The rear "HXM" houses the heat exchanger, fans, and flow meter.

A USB port is integrated for viewing and logging of temperature and sensor data using the [Koolance System Monitor](#) application. Rev.2.0 ALX systems add software control options for temperature set point, alarm, trigger relay,

pump speed, and fan speed.


- Cooling capacity: 750W (2559BTU/hr) with 25°C liquid-ambient delta @ 5.5LPM
- Temperature in °C/°F with set-point based on: liquid (-30 to 90°C), or one of two optional K-type thermocouples (-20 to 120°C)
- Pump: 10 manual levels, up to 5.5LPM (1.5GPM)
- Select only values you want displayed on the front 2-line OLED display (fixed or rotating)
- Show coolant flow rate in LPM/GPM
- Show pump impeller speed in RPM
- Show radiator fan speed in RPM
- Enable audio alarm based on: temperature, flow rate, and/or reservoir coolant level
- Enable relay trigger (NO or NC) based on: temperature, flow rate, and/or reservoir coolant level
- Power input: 12VDC, 49W or higher
- Reservoir capacity: 400ml (13.5 fl oz)
- 1/4 NPT threads on back for fittings

NOTE: Requires 12VDC input power. Koolance offers a separate [power supply](#) for AC wall outlet sources. Inlet/outlet fitting threads on rear of the cooling system are NPT 1/4-inch.


General	
Weight	8.00 lb (3.63 kg)
Fitting Thread	NPT 1/4
Max Pressure @ 25°C	2kgf/cm2 (28.5psi)
Max Temperature	60°C (140°F)
Noise (dBA)	30-58
Cooling Systems	
Cooling Capacity	750W (2559BTU/hr) @ 25°C liquid-ambient (25°C dT)
Display Type	OLED
Flow Rate	5.5LPM (1.5GPM)

General	
Max Power Consumption	49W
Power Source	12 VDC
Radiator	Brass/Copper, 1 x 120mm fan
Temperature Sensors	Liquid & Two K-Type Thermocouples (optional)
Temperature Stability	+/-0.5°C


ALX System Pump Output









ALX Systems
 $(\Delta T = \text{Inlet Water} - \text{Ambient} = 25^\circ\text{C})$



ALX Systems
($\Delta T = \text{Inlet Water} - \text{Ambient} = 25^\circ\text{C}$)





NO.	DISCRIPTION				MATER'L		QUANTITY	REMARKS
					UNIT	MM		
	KOOLANCE				SCALE	N/S	ITEM	ALX-750-P400
DATE					BY	BY	BY	APPRO BY
	S.J.LEE				CODE NO.	DWG. NO.	PAGE	