

**ALX-750-P400 Modular Liquid Cooling System  
(Rev.3.0)**



ALX-750-P400 contains a one-fan copper/brass radiator, providing about 750W of cooling with a 25° C liquid-ambient delta. Coolant flow rate, temperature, and reservoir level are monitored, and a USB port allows control and logging of most features using the [Koolance System Monitor](#) application.

This version includes the RPM-ALX400 and HXM-ALX750 modules, which are quickly combined during installation. This allows for the [radiator to be changed](#) to another size if cooling requirements later change. The front "RPM" contains the pump, reservoir, electronics, and sensors. The rear "HXM" houses the heat exchanger, fans, and flow meter.


- Cooling capacity: 750W (2559BTU/hr) with 25° C liquid-ambient delta @ 5.5LPM
- Temperature in °C/°F with set-point based on: liquid, or one of two optional K-type thermocouples
- Pump: 10 manual levels, up to 5.5LPM (1.5GPM)
- Select only values you want displayed on the front 2-line OLED display (fixed or rotating)
- Show coolant flow rate in LPM/GPM
- Show pump impeller speed in RPM
- Show radiator fan speed in RPM
- Enable audio alarm based on: temperature, flow rate, and/or reservoir coolant level
- Enable relay trigger (NO or NC) based on: temperature, flow rate, and/or reservoir coolant level
- Power input: 12VDC, 49W or higher
- Reservoir capacity: 600ml (20.3 fl oz)
- 1/4 NPT threads on back for fittings

NOTE: Requires 12VDC input power. Koolance offers a separate [power supply](#) for AC wall outlet sources. Inlet/outlet fitting threads on rear of the cooling system are NPT 1/4-inch.


General	
Weight	8.00 lb (3.63 kg)
Fitting Thread	NPT 1/4
Max Pressure Tolerance @ 25° C	1.5kgf/cm2 (21.3psi)
Max Temperature Tolerance	60° C (140° F)
Min Temperature Tolerance (*No Freezing)	-20° C (-4° F)
Noise (dBA)	30-58
Cooling Systems	
Cooling Capacity	750W (2559BTU/hr) @ 25° C liquid-ambient (25° C dT)
Display Type	OLED
Max Flow Rate (10-13mm ID)	5.5LPM (1.5GPM)
Max Power Consumption	49W
Max Static Pressure (10-13mm ID)	0.4kgf/cm2 (6psi)

General	
Power Source	12 VDC
Radiator	Brass/Copper, 1 x 120mm fan
Temperature Sensors	Liquid & Two K-Type Thermocouples (optional)
Temperature Stability	+/-0.5°C


ALX Systems  
 $(\Delta T = \text{Inlet Water} - \text{Ambient} = 25^\circ\text{C})$








ALX Systems  
 $(\Delta T = \text{Inlet Water} - \text{Ambient} = 25^\circ\text{C})$



## ALX System Pump Output





NO.	DISCRIPTION				MATER'L		QUANTITY	REMARKS
					UNIT	MM		
					SCALE	N/S	TITLE	Ass'y
DATE					BY	BY	BY	
MAR.13.2026	S.J.LEE					CODE NO.	DWG. NO.	PAGE