


QD3 Female Quick Disconnect No-Spill Coupling, Female Threaded G 1/4 BSPP




Koolance patented quick disconnect no-spill coupling with automatic shutoff. Opposite is a female G 1/4 BSPP thread for attaching a fitting or barb. The disconnect side will only fit a Koolance QD3 male quick disconnect.

After pulling the ring on the female QDC side, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with approximately 0.2ml freed. Coolant volume lost upon disconnection will rise with internal pressure higher than 0.5kgf/cm² (7psi).

General	
Weight	0.17 lb (0.08 kg)
Max No-Spill Pressure	0.5kgf/cm ² (7psi)
Max Pressure Tolerance @ 25° C	8kgf/cm ² (113.8psi)
Max Temperature Tolerance	80° C (176° F)
Min Pressure Tolerance @ 25° C	-1.0kgf/cm ² (-14psi)
Min Storage Temperature (*No Freezing)	-20° C (-4° F)
Seal Material	EPDM (Water/Glycol Liquids)
Wetted Materials	Brass, Nickel Plating, Stainless Steel, EPDM





REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
REVISION					

NO.	DISCRIPTION				MATER'L		QUANTITY	REMARKS				
KOOLANCE INC.					DECIMAL PLACES	INCHES	MILLIMETRES	UNIT	MM	ITEM	QD3	
					.XXX	±.005	±0.1	SCALE	N/S	TITLE	QD3-FSFG4	
DATE					.XX	±.010	±0.3	3RD ANGLE				
					.X	±.020	±0.5					
BY					ANGULAR DIMENSIONS			CODE NO.		DWG. NO.		PAGE
					XX'	±0.5'						
SONG					XX.X'	±0.1'						
					SURFACE ROUGHNESS							SURFACE
												.63