





Radiator, 1x120mm 18-FPI Aluminum




HX-422 is a low profile aluminum radiator designed for one 120mm fan. With a fin density of 18 FPI (fins per inch), it is optimized for quieter air flow ranges. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).

General	
Weight	1.25 lb (0.57 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	20kgf/cm2 (284.5psi)
Max Temperature Tolerance	200° C (392° F)
Wetted Materials	Aluminum
Radiators	
Fan Capacity	1 x 120mm
Fins Per Inch (FPI)	18







NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
		UNIT	MM	ITEM HX-422
		SCALE	N/S	TITLE
DATE	BY	BY	BY	BY
				3RD ANGLE
	S.J.LEE			CODE NO.
				DWG. NO.
				PAGE

KOOLANCE INC.

Ass'y