





HX-CU720V is a low profile copper core radiator designed for two 120mm fans. With a fin density of 30 FPI (fins per inch), it offers best performance with higher air flow. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).


General	
Weight	1.30 lb (0.59 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	1.5kgf/cm2 (21psi)
Max Temperature Tolerance	150° C (302° F)
Wetted Materials	Brass/Copper
Radiators	
Fan Capacity	2 x 120mm
Fins Per Inch (FPI)	30




Koolance HX-CUxxxV Heat Exchangers
(10/13mm ID Nozzle)




HX-CU720V
($\Delta T = \text{Inlet Water} - \text{Ambient} = 15^\circ\text{C}$)




HX-CU720V
($\Delta T = \text{Inlet Water} - \text{Ambient} = 25^\circ\text{C}$)




HX-CU720V
($\Delta T = \text{Inlet Water} - \text{Ambient}$)





REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
REVISION					

NO.		DESCRIPTION				MATER'L		QUANTITY	REMARKS	
						UNIT	MM	ITEM HX-CU720V		
						SCALE	N/S	TITLE		
DATE		BY	BY	BY	APPRO BY	3RD ANGLE		Ass'y		
S.J.LEE						CODE NO.		DWG. NO.		PAGE