





HX-CU720V is a low profile copper core radiator designed for two 120mm fans. With a fin density of 30 FPI (fins per inch), it offers best performance with higher air flow. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).


General	
Weight	1.30 lb (0.59 kg)
Fitting Thread	G 1/4 BSPP
Materials	Brass/Copper
Max Pressure @ 25 °C	2kgf/cm2 (28.5psi)
Max Temperature	150 °C (302 °F)
Radiators	
Fan Capacity	2 x 120mm
Fins Per Inch (FPI)	30




HX-CU720V  
 ( $\Delta T = \text{Inlet Water} - \text{Ambient} = 25^\circ\text{C}$ )




Koolance HX-CUxxxV Heat Exchangers  
 (10/13mm ID Nozzle)




HX-CU720V  
 ( $\Delta T = \text{Inlet Water} - \text{Ambient}$ )



HX-CU720V  
( $\Delta T = \text{Inlet Water} - \text{Ambient} = 15^\circ\text{C}$ )





REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
REVISION					

NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
		UNIT	MM	ITEM HX-CU720V
		SCALE	N/S	TITLE
DATE	BY	BY	BY	BY
	S.J.LEE			
		3RD ANGLE		
		CODE NO.	DWG. NO.	PAGE