





HX-CU1020V is a low profile copper core radiator designed for three 120mm fans. With a fin density of 30 FPI (fins per inch), it offers best performance with higher air flow. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).


| General | |
|--------------------------------|--------------------|
| Weight | 1.90 lb (0.86 kg) |
| Fitting Thread | G 1/4 BSPP |
| Max Pressure Tolerance @ 25 °C | 1.5kgf/cm2 (21psi) |
| Max Temperature Tolerance | 150 °C (302 °F) |
| Wetted Materials | Brass/Copper |
| Radiators | |
| Fan Capacity | 3 x 120mm |
| Fins Per Inch (FPI) | 30 |




HX-CU1020V
 ($\Delta T = \text{Inlet Water} - \text{Ambient}$)



Koolance HX-CUxxxV Heat Exchangers
 (10/13mm ID Nozzle)



Koolance HX-CUxxxV Heat Exchangers
 (6mm ID Nozzle)



HX-CU1020V
($\Delta T = \text{Inlet Water} - \text{Ambient} = 15^\circ\text{C}$)

