





The HX-1320 provides an approximate 1300W of added heat dissipation when coupled with four 120mm fans. Vertical (perpendicular) G 1/4 BSPP (parallel) thread fitting sockets. Four 0.28" (7mm) long and sixteen 1.4" (35mm) long mounting screws are included. Dual pass, 15mm (0.59") fan hole spacing.

General	
Weight	3.75 lb (1.70 kg)
Materials	Aluminum
Radiators	
Fan Capacity	4 x 120mm
Fins Per Inch (FPI)	18


HX-1320



4 Fan AL Radiator (HX-1320)
($\Delta T = \text{Inlet Water} - \text{Ambient}$)



4 Fan AL Radiator (HX-1320)
 ($\Delta T = \text{Inlet Water} - \text{Ambient} = 15^\circ\text{C}$)



4 Fan AL Radiator (HX-1320)
 ($\Delta T = \text{Inlet Water} - \text{Ambient} = 25^\circ\text{C}$)

