




The copper core HX-CU1320H provides an approximate 1300W of added heat dissipation when coupled with four 120mm fans. With a fin density of 20 FPI (fins per inch), it is optimized for low to mid-range air flow. Horizontal (parallel) G 1/4 BSPP (parallel) thread fitting sockets. 32mm (1.26") long mounting screws are included. Dual pass, 15mm (0.59") fan hole spacing.

General	
Weight	3.75 lb (1.70 kg)
Wetted Materials	Brass/Copper
Radiators	
Fins Per Inch (FPI)	20



Koolance HX-CUxxxH Heat Exchangers
(6mm ID Nozzle)

