


QDT2 Viton Male Quick Disconnect No-Spill Coupling, Male Threaded, 1/4 NPT





Koolance patented quick disconnect no-spill coupling with automatic shutoff. 1/4 NPT (tapered) male fitting for screwing directly into a component of the same threading. It will only fit a Koolance QDT2 female quick disconnect.

After pulling the ring on the female QDC side, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with approximately 0.2ml freed.

General	
Weight	0.08 lb (0.04 kg)
Fitting Thread	NPT 1/4
Max No-Spill Pressure	10kgf/cm2 (142psi)
Max Pressure Tolerance @ 25°C	12kgf/cm2 (170.7psi)
Max Temperature Tolerance	80°C (176°F)
Min Pressure Tolerance @ 25°C	-1.0kgf/cm2 (-14psi)
Min Storage Temperature (*No Freezing)	-40°C (-40°F) Connected, -30°C (-22°F) Disconnected
Seal Material	Viton (Oil Liquids)
Wetted Materials	Chrome-Plated Brass, Stainless Steel, Viton





REV	DATE	CONTENTS	APPD BY
REVISION			

NO.		DESCRIPTION		MATER'L		QUANTITY	REMARKS
		BY		BY		UNIT	MM
						SCALE	N/S
DATE		BY		BY		3RD ANGLE	
		S.JLEE				DWG. NO.	
						ITEM	
						QDT2	

NO.		DESCRIPTION		MATER'L		QUANTITY	REMARKS
		BY		BY		UNIT	MM
						SCALE	N/S
DATE		BY		BY		3RD ANGLE	
		S.JLEE				DWG. NO.	
						ITEM	
						QDT2	