

**Reservoir and Pump, RP-1000SL, Silver**

The RP-1000 is a combined reservoir and pump unit which fits into a single 5.25" (CD) bay. Featuring the powerful Koolance [PMP-400](#) pump, it also includes temperature monitoring, a front LED display, reservoir, pump and fan speed control, and rear G 1/4in threaded fitting sockets.



**Features:**

- Fits a single 5.25" CD bay
- Adjusts radiator fan speeds automatically, or with 10 manual levels
- Manual pump speed adjustment
- Variable temperature alarms on 3 independent sensors
- Auto-cycle or static display of all connected temperature sensors
- Variable safety shutdown temperature
- Front and top reservoir blue LED lighting
- Top refill plug

**Pump:**

- Maximum Flow Rate: 8.7 L/min (2.3 gal/min)
- Maximum Head Pressure: 7m (23ft)
- Motor: Brushless DC, electronically commutated, spherical motor
- Power Consumption (at max): 20W
- Voltage Range: 8 to 13.2 VDC
- Electrical Connector: 3-pin fan header with tachometer speed signal

**IMPORTANT NOTE:** The RP-1000 pump should never be run dry. Always test this product with coolant.

| General             |                   |
|---------------------|-------------------|
| Weight              | 5.50 lb (2.49 kg) |
| Reservoirs          |                   |
| Capacity            | 237mL (8 fl oz)   |
| Display Type        | LED               |
| Pump                | PMP-400 @ 12V     |
| Temperature Sensors | 50K Thermistors   |



