


GPU-230 Cold Plate, 45mm x 45mm (1.8in x 1.8in)



GPU-230 is a general-purpose water block with a 0.5mm microfin internal structure. The cooling area footprint is approximately 45mm x 45mm (1.8in x 1.8in).

Materials include a copper cold plate, POM acetal top, anti-corrosive nickel plating, stainless steel, and EPDM o-rings. Works with G 1/4 BSPP (parallel) thread fittings. The diagonal hole distance supported by the mounting bracket is approximately 70-86mm.

Cold Plates	
Flow Resistance @ 5LPM (10-13mm ID)	0.056kgf/cm2 (0.8psi)
Thermal Resistance @ 5LPM (Approx.)	0.04°C/W
General	
Weight	0.63 lb (0.29 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	10kgf/cm2 (142.2psi)
Max Temperature Tolerance	100°C (212°F)
Wetted Materials	Nickel-Plated Copper, POM Acetal, Stainless Steel, EPDM



GPU-230

