








HX-422 is a low profile aluminum radiator designed for one 120mm fan. With a fin density of 18 FPI (fins per inch), it is optimized for quieter air flow ranges. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).

General	
Weight	1.25 lb (0.57 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	20kgf/cm2 (284.5psi)
Max Temperature Tolerance	200° C (392° F)
Wetted Materials	Aluminum
Radiators	
Fan Capacity	1 x 120mm
Fins Per Inch (FPI)	18







NO.		DESCRIPTION				MATER'L		QUANTITY	REMARKS
						UNIT	MM	ITEM	HX-422
						SCALE	N/S	TITLE	
						3RD ANGLE		Ass'y	
						CODE NO.		DWG. NO.	PAGE