





The copper core HX-CU420H provides an approximate 400W of added heat dissipation when coupled with one 120mm fan. With a fin density of 20 FPI (fins per inch), it is optimized for low to mid-range air flow. Horizontal (parallel) G 1/4 BSP (parallel) thread fitting sockets. 32mm (1.26") long mounting screws are included. Dual pass.

General	
Weight	1.30 lb (0.59 kg)
Max Pressure Tolerance @ 25 °C	3kgf/cm2 (42.7psi)
Max Temperature Tolerance	150 °C (302 °F)
Wetted Materials	Brass/Copper
Radiators	
Fins Per Inch (FPI)	20



Koolance HX-CU420H
($\Delta T = \text{Inlet Water} - \text{Ambient} = 25^\circ\text{C}$)



Koolance HX-CU420H
($\Delta T = \text{Inlet Water} - \text{Ambient} = 15^\circ\text{C}$)



Koolance HX-CUxxxH Heat Exchangers
(10/13mm ID Nozzle)



Koolance HX-CUxxxH Heat Exchangers
(6mm ID Nozzle)

