







The copper core HX-CU720H provides an approximate 700W of added heat dissipation when coupled with two 120mm fans. Offers excellent performance with low air flow. Horizontal (parallel) G 1/4 BSPP (parallel) thread fitting sockets. 32mm (1.26") long mounting screws are included. Dual pass, 15mm (0.59") fan hole spacing.

General	
Weight	2.25 lb (1.02 kg)
Wetted Materials	Brass/Copper
Radiators	
Fins Per Inch (FPI)	20





Koolance HX-CUxxxH Heat Exchangers
(10/13mm ID Nozzle)



Koolance HX-CUxxxH Heat Exchangers
(6mm ID Nozzle)

