



HX-1020 is a low profile aluminum radiator designed for three 120mm fans. With a fin density of 18 FPI (fins per inch), it is optimized for quieter air flow ranges, but will readily benefit from high CFM fans. It has a dual pass coolant design, with G 1/4 BSPP (parallel) threads for tube fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).

General	
Weight	3.25 lb (1.47 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25 °C	20kgf/cm2 (284.5psi)
Max Temperature Tolerance	200 °C (392 °F)
Wetted Materials	Aluminum
Radiators	
Fan Capacity	3 x 120mm
Fins Per Inch (FPI)	18





