





HX-CU1020V is a low profile copper core radiator designed for three 120mm fans. With a fin density of 30 FPI (fins per inch), it offers best performance with higher air flow. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).


General	
Weight	1.90 lb (0.86 kg)
Fitting Thread	G 1/4 BSPP
Materials	Brass/Copper
Max Pressure Tolerance @ 25°C	2kgf/cm2 (28.5psi)
Max Temp. Operating Tolerance	150°C (302°F)
Radiators	
Fan Capacity	3 x 120mm
Fins Per Inch (FPI)	30




Koolance HX-CUxxxV Heat Exchangers
(10/13mm ID Nozzle)



Koolance HX-CUxxxV Heat Exchangers
(6mm ID Nozzle)



HX-CU1020V
($\Delta T = \text{Inlet Water} - \text{Ambient} = 15^\circ\text{C}$)



HX-CU1020V
($\Delta T = \text{Inlet Water} - \text{Ambient}$)

