





HX-CU1320V is a low profile copper core radiator designed for four 120mm fans. With a fin density of 30 FPI (fins per inch), it offers best performance with higher air flow. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).


| General                        |                    |
|--------------------------------|--------------------|
| Weight                         | 2.70 lb (1.22 kg)  |
| Fitting Thread                 | G 1/4 BSPP         |
| Max Pressure Tolerance @ 25 °C | 1.5kgf/cm2 (21psi) |
| Max Temperature Tolerance      | 150 °C (302 °F)    |
| Wetted Materials               | Brass/Copper       |
| Radiators                      |                    |
| Fan Capacity                   | 4 x 120mm          |
| Fins Per Inch (FPI)            | 30                 |




HX-CU1320V  
 $(\Delta T = \text{Inlet Water} - \text{Ambient} = 15^\circ\text{C})$



HX-CU1320V  
 $(\Delta T = \text{Inlet Water} - \text{Ambient})$



HX-CU1320V  
 $(\Delta T = \text{Inlet Water} - \text{Ambient} = 25^\circ\text{C})$



Koolance HX-CUxxxV Heat Exchangers  
(10/13mm ID Nozzle)

