







HX-CU1320V is a low profile copper core radiator designed for four 120mm fans. With a fin density of 30 FPI (fins per inch), it offers best performance with higher air flow. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).

| General | |
|--------------------------------|--------------------|
| Weight | 2.70 lb (1.22 kg) |
| Fitting Thread | G 1/4 BSPP |
| Max Pressure Tolerance @ 25° C | 1.5kgf/cm2 (21psi) |
| Max Temperature Tolerance | 150° C (302° F) |
| Wetted Materials | Brass/Copper |
| Radiators | |
| Fan Capacity | 4 x 120mm |
| Fins Per Inch (FPI) | 30 |





Koolance HX-CUxxxV Heat Exchangers
(10/13mm ID Nozzle)

